



CR-2

v.1.2.1.12

SN:00214

T

100/50 mm³/h cm³/10004/30/2018
2:39:31 AM

Siemens

CRI

Piezo

1.

BK2Q-9K546-AG

CODING IIC

1

96EFEG

98DEHF

	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
RL	1350	----	----	1000	36.7°	----	35.0 ±25.0
				----	T _i , °C	, ³	, ³
	1		✓		21.0°	----	27.8
	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
RL	250	----	----	1000	36.2°	----	5.0 ±3.0
				----	T _i , °C	, ³	, ³
	1		✓		21.2°	----	5.12
	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
VE	800	----	----	1000	40.5°	1.9 ±1.5	----
				IIC	T _i , °C	, ³	, ³
	1		✓	✓	21.5°	1.91	6.93
	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
LL	250	----	----	1000	40.1°	8.1 ±3.0	----
				IIC	T _i , °C	, ³	, ³
	1		✓	✓	20.6°	8.40	5.46
	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
EM	1200	----	----	1000	39.5°	35.6 ±6.0	----
				IIC	T _i , °C	, ³	, ³
	1		✓	✓	20.3°	35.3	19.9
	P _i	t _i	U _i	n _i 1/	T _i , °C	, ³	, ³
VL	1600	----	----	1000	39.3°	71.2 ±12.0	----
				IIC	T _i , °C	, ³	, ³
	1		✓	✓	21.7°	69.8	47.3