



CR-2

v.1.2.1.12

SN:00214

T

100/50 mm³/h cm³/10004/30/2018
2:04:07 AM

Siemens

CRI

Piezo

1.

BK2Q-9K546-AG

CODING IIC

1

96EFEG

9BDGEH

	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
RL	1350	----	----	1000	38.7°	----	35.0 ±25.0
				----	T _i , °C	, ³	, ³
	1		✓		19.3°	----	25.3
	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
RL	250	----	----	1000	41.2°	----	5.0 ±3.0
				----	T _i , °C	, ³	, ³
	1		✓		19.6°	----	5.15
	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
VE	800	----	----	1000	41.2°	1.9 ±1.5	----
				----	T _i , °C	, ³	, ³
	1		✓	✓	20.0°	2.11	5.63
	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
LL	250	----	----	1000	40.5°	7.8 ±3.0	----
				----	T _i , °C	, ³	, ³
	1		✓	✓	19.5°	7.74	5.19
	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
EM	1200	----	----	1000	39.3°	35.2 ±6.0	----
				----	T _i , °C	, ³	, ³
	1		✓	✓	19.0°	35.5	17.2
	P _i	t _i	U _i	n, 1/	T _i , °C	, ³	, ³
VL	1600	----	----	1000	37.8°	70.9 ±12.0	----
				----	T _i , °C	, ³	, ³
	1		✓	✓	19.7°	69.7	42.8