



www.ditex.it


#0445115069

WORKSHOP	SIA DISTEHNKA
CUSTOMER #ID	02.22.0001
EMAIL	info@distehnika.lv
ORDER #ID	

2008 SEP

EQUIPMENT #1	CRI 1000 S
EQUIPMENT #2	CRI 1000 NEW STYLE
EQUIPMENT #3	DX73625+DX73615
ADAPTOR	

DELIVERY PIPE	DX73260
BACKLEAKAGE PIPE	DX73253+DX73261
CURRENT PROFILE	3
INJ TYPE	PIEZO

	DX73780	MIN	MAX
	RESISTANCE Ω		
	INDUCTANCE μH		
	CAPACITANCE μF		

INJ 1	INJ 2	INJ 3	INJ 4	INJ 5	INJ 6

#	RAIL PRESSURE	CRI 1000 S	Q_MIN	Q_MAX	BL
	BAR	OPENING TIME pos/μsec	cm ³ /1000 strokes	cm ³ /1000 strokes	cm ³ /1000 strokes
A	500	OFF	3 min		
B	500→800	pos 5			>1
1	1600	pos 4			20
			38,6	45,4	
2	800	pos 3	16,6	21,8	
3	800	pos 1	2,8	3,6	
4	250	pos 4	2,2	4,2	
5					
6					
7	1600→130	OFF	0,0	NO DX73260	

SO 4113 40°C ± 2°C

[illegible]